



Precompliance test antenna series HyperLOG[®] 60xxx span 680MHz to 18GHz

One logper antenna for the complete frequency range from 680MHz to 18GHz

Highlights:

- Optimal for usage with spectrum analysers for EMC measurement
- Top-quality high-tech TEFLON antenna support
- Excellent forward/backward ratio
- Freely alignable polarisation
- Excellent symmetry of radiation patterns
- Integrated 1/4" tripod socket
- Suitable for mobile use
- Made in Germany
- 10 years warranty

Calibration & standards:

- The log-periodic precompliance test antenna of the HyperLOG[®] 60xxx series are suitable for interference field strength measurement. The specialized broadband characteristics allow measurements to be taken in the complete specified frequency range without switching.
- These antennas are suitable for measurement according to the following standards and procedures:

CISPR, VDE, MIL, VG, EN 55011, EN 55013, EN 55015, EN 55022, MIL-Std-461.

Included with delivery:

- HyperLOG[®] 60xxx-Antenna
- Typical calibration data with up to 1734 calibration points (10MHz steps)
- Aluminum design carrycase with custom padding
- Sturdy, detachable pistol grip with "miniature tripod" mode
- Special Aaronia SMA toolset with overtorque protection

References / examples of proof:

- BMW, München, Germany
- Hewlett Packard, Dornach, Germany
- Audi AG, Ingolstadt, Germany
- DLR, Köln, Germany
- University of Florida, USA
- IBM, Stuttgart, Germany

Specifications

HyperLOG[®] 6080:


- Design: Logarithmic-periodic
- Frequency range: 680MHz-8GHz
- Max. transmission power: 100 W CW (400MHz)
- Nominal impedance: 50 Ohms
- VSWR (typ.): <1:2,5
- Gain (typ.): 5dBi
- Antenna factor: 22-44dB/m
- Calibration points: 733 (10MHz steps)
- RF connection: SMA socket (18GHz) or N socket using an adapter
- Dimensions (L/W/D): (340x200x25) mm
- Weight: 250gr
- Warranty: 10 years


HyperLOG[®] 60100:

- Design: Logarithmic-periodic
- Frequency range: 680MHz-10GHz
- Max. transmission power: 100 W CW (400MHz)
- Nominal impedance: 50 Ohms
- VSWR (typ.): <1:2,5
- Gain (typ.): 5dBi
- Antenna factor: 22-46dB/m
- Calibration points: 933 (10MHz steps)
- RF connection: SMA socket (18GHz) or N socket using an adapter
- Dimensions (L/W/D): (340x200x25) mm
- Weight: 250gr
- Warranty: 10 years


HyperLOG[®] 60180:

- Design: Logarithmic-periodic
- Frequency range: 680MHz-18GHz
- Max. transmission power: 100 W CW (400MHz)
- Nominal impedance: 50 Ohms
- VSWR (typ.): <1:2,5
- Gain (typ.): 5dBi
- Antenna factor: 22-50dB/m
- Calibration points: 1733 (10MHz steps)
- RF connection: SMA socket (18GHz) or N socket using an adapter
- Dimensions (L/W/D): (340x200x25) mm
- Weight: 250gr
- Warranty: 10 years







Antenna factor HyperLOG 60100




Antenna factor HyperLOG 60180



Horizontal Pattern HyperLOG 60xx Series



Vertikal Pattern HyperLOG 60xx Series



Description



HyperLOG 70xx Antenna with pistol grip expanded as a miniature tripod

The HyperLOG® 60xxx logper antennas come standard with a specially constructed, high tech radom housing. This housing has been constructed after intense research with the most modern computer technology in such a way that its shape, material and special coating have virtually no influence on measurements, not even in case of dew or other kinds of humidity collecting on the surface. Another important factor for Aaronia was the development of a radom with the lowest possible damping factor achievable. This turned out to be quite an adventure for our development team, particularly in the high GHz ranges. Fortunately, this adventure has been mastered resulting in a beautiful, elegant design, to the complete satisfaction of the development team. Our first test measurements even by far surpassed our guidelines!

The resulting antenna had the best possible protection against mechanical stress and environmental influence without sacrificing any of its performance. With their log-periodic measurement antennas from the HyperLOG® 60xxx series, Aaronia finally offers a very cost-effective alternative, which at the same time meets the highest expectations. In conjunction with the HyperLOG® antennas, every regular spectrum analyser becomes a fully professional directional RF measurement device within a few moments. Thus, a perfect "dream team" for EMC measurement in the laboratory or for outdoor use is at your disposal.

Due to their small weight and the multi-functional handle, these antennas are the optimal supplement for portable EMC measurement devices for locating and evaluating any kind of signal source.



Also available in a "transparent" finish at extra charge

Included with delivery: A sturdy aluminum design carrycase with custom padding for the antenna, cables and accessories. Furthermore, every antenna of the HyperLOG[®] 60xxx series includes a detachable multi-functional pistol grip with "miniature-tripod" mode and an appropriate SMA toolset.



Lot of space for optionally accessories: The HyperLOG[®] transportcase

Recommended accessories for Aaronia Antennas

Aluminum tripod

Height adjustable, high stability. Recommended for use with HyperLOG 70xx and 60xx antennas. Max. height: 105cm.

Order/Art.-No.: 281



1m / 5m / 10m SMA-Cable

High quality special SMA cable for connecting any HyperLOG[®]-Antenna or BicoLOG[®]-Antenna with various test equipment like our RF Spectrum-Analyzer. You can choose between 3 different cables:

1m standard SMA cable (RG316U) 5m LowLoss SMA cable (especially low damping) 10m LowLoss SMA cable (especially low damping)

All versions: SMA plug (male) / SMA plug (male) Order/Art.-No.: 771 (1m Cable), 772 (5m Cable), 773 (10m Cable)



SMA to N Adapter

This special high quality adapter allows operation of all HyperLOG[®]-Antenna with any standard spectrum-analyzer with N connector. Also this adapter is needed to connect BicoLOG[®] antennas to a SPECTRAN Spectrum Analyzer.

Especially massive, chrome-plated design. This adapter is usable for very high frequencies up to at least 18GHz. Physical dimensions are just 30x20mm. Nominal impedance 50 Ohms. Layout: SMA socket (female) / N plug (male).

Order/Art.-No.: 770

Heavy multifunctional Pistol Grip (strongly recommended!)

Highly recommend for the usage of HyperLOG antennas. Quick and easy change of antenna polarization, perfect antenna handling (even with the more heavy HyperLOG 30100X).

Order/Art.-No.: 282





Frequency overview Analyzer & Antennas

Frequency Overview SPECTRAN Spectrum Analyzer

1Hz	10Hz	100Hz	1kHz	10kHz	100kHz	1	МНz		10MHz		100MHz	1GHz		10¢Hz	100GHz	
	SPECTRAN	NF-1010E														
	SPECTRAN	NF-3020														
SPECTRA	N NF-5030 (op	t. 30MHz)														
SPECTRA	N NF-XFR (opt.	30MHz)														
												SPECT	AN H	-2025E Rev	3	
											SPECTRAN	HF-404	<mark>10</mark> Rev	3		
									SPECTR	AN F	HF-6060 VH					
									SPECTR	AN F	HF-6080 VH					
						S	PECTR	RAN I	IF-60100	V٩						
						S	PECTR	RAN I	HF-XFR							

Frequency Overview HyperLOG and BicoLOG Antennas and Probes

Image: Control of the second of the secon	1Hz	10Hz	100Hz	1kHz	10kHz	100kHz	1MHz	10MHz	100MHz		10ĢHz	100GHz
Image: State Stat												
Image: Construction of the second of the										HyperLOG 703	25 X	
Image: Constraint of the second se												
Image: Construction of Constructin of Constructin of Construction of Constructi												
Image: Construction of the second												
Image: Control of the second secon												
Image: Sector												
Image: Construction of the second of the										HyperLOG 60	30 X	
Arronia EMV Probe-Set PBS1 & PBS2 Arronia GEO Serie()												
Image: Sector of the sector											80	
Image: Constraint of the second of the se										HyperLOG 4025		
HyperLOG 40 40 X HyperLOG 40 40 X HyperLOG 40 40 X HyperLOG 40 40 X HyperLOG 40 50 X HyperLOG 30 80 HyperLOG 30 100 HyperLOG 30 100 BicoLOG 50 70 BicoLOG 30 100 BicoLOG 30 100 BicoLOG 30 100 BicoLOG 20 100										HyperLOG 4025 }	4	
HyperLOG 4060 HyperLOG 3080 HyperLOG 30100 HyperLOG 30180 HyperLOG 2000 EMI OmniLOG 90200 Image: HyperLOG 30100												
Image: Construction of the second state of the second s										HyperLOG 4040 }		
Image: Source of the second												
Image: Solution of the second sec												
HyperLOG 30100 HyperLOG 30180 HyperLOG 30180 HyperLOG 20300 EMI HyperLOG 20600 EMI HyperLOG 20600 EMI OmniLog 690 200 BicoLOG 5070 BicoLOG 30100 BicoLOG 30100 BicoLOG 30100 BicoLOG 30100 BicoLOG 20100												
HyperLOG 30180 HyperLOG 20300 EMI HyperLOG 20300 EMI HyperLOG 20600 EMI OmniLD G90200 BicoLOG 5070 BicoLOG 30100E BicoLOG 30100E BicoLOG 20100E												
HyperLOG 20300 EMI HyperLOG 20600 EMI MyperLOG 20600 EMI OmniLOG90200 BicoLOG 5070 BicoLOG 30100 BicoLOG 30100 BicoLOG 30100E BicoLOG 20100 BicoLOG 20300 BicoLOG 20300 BicoLOG 20300										HyperLOG 30100		
HyperLOG 20600 EMI OmniLOG90200 BicoLOG 5070 BicoLOG 30100E BicoLOG 30100E BicoLOG 20100 BicoLOG 20100E BicoLOG 20100E BicoLOG 20300 BicoLOG 20300 Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)												
Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)												
BicoLOG 5070 BicoLOG 5070 BicoLOG 30100E BicoLOG 30100E BicoLOG 20100 BicoLOG 20100E BicoLOG 20300 BicoLOG 20300 Aaronia EMV Probe-Set PBS1 & PBS2 BicoLOG 20300 Aaronia Active Differential Probe (NF-50xx series) BicoLOG 20100E								HyperL	06 20600		No.	
BicoLOG 30100 BicoLOG 30100E BicoLOG 20100 BicoLOG 20100E BicoLOG 20100E BicoLOG 20100E BicoLOG 20300 Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)												
BicoLOG 30100E BicoLOG 20100 BicoLOG 20100E BicoLOG 20100E BicoLOG 20100E BicoLOG 20300 Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)									00.00100			
BicoLOG 20100 BicoLOG 20100E BicoLOG 20300 BicoLOG 20300 Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)								BICOL	00 30100			
Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)												
Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)								Disel O	0 20100			
Aaronia EMV Probe-Set PBS1 & PBS2 Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)												
Aaronia Active Differential Probe (NF-50xx series) Geophon (Aaronia GEO Series)	Anvonia	Drobos Sot D	0 0 1 0 00 00					BICOLO	8 20300			
Geophon (Aaronia GEO Series)				() ()								
	Maronia											
	subHz				4 E	F	ME	-F	/HE			